



YTU30R26R, Aluminum T-Tap Connector

By Burndy
Catalog # YTU30R26R



Al Compression T-Tap Connector, 266.8 kcmil ACSR, 300 kcmil 266.8 kcmil 250 kcmil Al, 300 - 250 kcmil Cu(Run), 2/O AWG ACSR/Al/Cu(Tap).

General

| | |
|---------------------------|----------------|
| Catalog Number | YTU30R26R |
| Connector Type | Tap |
| Material | Aluminum Alloy |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| UPC | 781810373095 |
| UPC 12 Digit | 7818103730955 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 1.88 in |
| Dimension - Height inch | 3.54 in |
| Dimension - L Length Overall mm | 217 mm |
| Dimension - Length Overall inch | 8.58 in |

Conductor Related

| | |
|----------------------------------|------------------------|
| Conductor - ACSR Str Run | 266.8 kcmil |
| Conductor - ACSR Str Tap | 2/O AWG(6-1 STR) |
| Conductor - AL Str Run | 266.8 kcmil, 300 kcmil |
| Conductor - AL Str Run Range | 266.8 kcmil-300 kcmil |
| Conductor - AL Str Tap | 2/O AWG(7,19 STR) |
| Conductor - Copper Str Run | 250 kcmil, 300 kcmil |
| Conductor - Copper Str Run Range | 250 kcmil-300 kcmil |
| Conductor - Copper Str Tap | 2/O AWG(7,19,12 STR) |

Certifications And Compliance

| | |
|-------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 2 |
|-----------------------|---|

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD031286](#)
- [Specifications - YTU30R26R](#)