



YTU30R30R, Aluminum T-Tap Connector

By Burndy
Catalog # [YTU30R30R](#)



Al Compression T-Tap Connector, 266.8 kcmil ACSR, 300 - 250 kcmil Cu/Al (Run & Tap).

General

Connector Type	Tap
Die Index Run Side	M
Die Index Tap Side	M
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810155608
UPC 12 Digit	7818101556088

Dimensions

Dimension - B Length inch	2.67 in
Dimension - Height inch	4.32 in
Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in

Conductor Related

Conductor - ACSR Str Run	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil-266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Tap	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil
Conductor - ACSR Str Tap Range	266.8 (18/1) Waxwing kcmil-266.8 (26/7) Owl kcmil
Conductor - AL Str Run	266 kcmil;300 kcmil
Conductor - AL Str Run Range	266 kcmil-300 kcmil
Conductor - AL Str Tap	266 kcmil;300 kcmil
Conductor - AL Str Tap Range	266 kcmil-300 kcmil
Conductor - Copper Str Run	250 kcmil;300 kcmil
Conductor - Copper Str Run Range	250 kcmil-300 kcmil
Conductor - Copper Str Tap	250 kcmil(12,19,37 STR), 300 kcmil(19,37 STR)
Conductor - Copper Str Tap Range	250 kcmil(12,19,37 STR)-300 kcmil(19,37 STR)

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD031286](#)



A proud member of the Hubbell Family.

