



YTU321R25R, Aluminum T-Tap Connector

By Burndy
Catalog # [YTU321R25R](#)



Al Compression T-Tap Connector, 300 - 336.4 kcmil
ACSR,6201,5005, 350 - 336.4 kcmil Al, 350 kcmil Cu(Run), 1/0
AWG ACSR/Al/Cu(Tap).

General

Catalog Number	YTU321R25R
Connector Type	Tap
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810298404
UPC 14 Digit GTIN	00781810298404

Dimensions

Dimension - B Length inch	2.09 in
Dimension - Height inch	3.81 in
Dimension - Height mm	84 mm
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.09 in

Conductor Related

Conductor - ACSR Str Run	336.4 kcmil, 300 kcmil
Conductor - ACSR Str Run Range	300 kcmil-336.4 kcmil
Conductor - ACSR Str Tap	1/0 AWG(6-1 STR)

Conductor - AL Str Run	350 kcmil, 336.4 kcmil
Conductor - AL Str Run Range	336.4 kcmil-350 kcmil
Conductor - AL Str Tap	1/0 AWG(7,19 STR)
Conductor - Copper Str Run	350 kcmil
Conductor - Copper Str Tap	1/0 AWG(7,19,12 STR)

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD031286](#)
- [Specifications - YTU321R25R](#)