



# YTW32R34REKHT, Single Pad Full Tension Deadend for ACSS

By Burndy  
Catalog # [YTW32R34REKHT](#)



Single Pad Full Tension Compression Deadend for ACSS Conductor.

## General

|                                      |               |
|--------------------------------------|---------------|
| Connector Type                       | Deadend       |
| Feature - Barrel Style               | Tapered       |
| Material                             | Aluminum      |
| Physical Attribute - Number of Holes | 4             |
| UPC                                  | 781810516188  |
| UPC 12 Digit                         | 7818105161888 |

## Dimensions

|   |          |
|---|----------|
| Dimension - B Length fraction             | 2-1/2 in |
| Dimension - B Length inch                 | 2.50 in  |
| Dimension - Bolt Size fraction            | 1/2      |
| Dimension - F Width Center to Center inch | 1.75 in  |
| Dimension - Hole Size inch                | 0.88 in  |
| Dimension - Length Overall inch           | 21.53 in |
| Dimension - Pad Width inch                | 3.25 in  |
| Dimension - Width inch                    | 0.62 in  |

## Conductor Related

Conductor - ACSS Str Size 336.4 (26/7) kcmil

## Certifications and Compliance

Certification - CSA Approved No  
Standards - RoHS Compliance UI  
Status

## Logistics

Minimum Pack Quantity 1

## Product Assets

[Sales Drawings - 50018275](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YTW32R34REKHT-SPEC-EN | REV 8/2023