



YTW430MMRC15ACK5LS, Full Tension Deadend for Brussels ACCC

By Burndy
Catalog # [YTW430MMRC15ACK5LS](#)

Full Tension, BRUSSELS ACCC® Deadend Connector, Accommodates 430 mm131.



*Representative Image

Application

For ACCC Conductor, Corona free operation up to 230 KV

General

Connector Type	Deadend
Prefilled Oxide Inhibitor	N
UPC	781810551936
UPC 12 Digit	7818105519366

Dimensions

Dimension - Inside Diameter inch	1.09 in
Dimension - Length Overall inch	15.5 in
Dimension - Outside Diameter inch	1.32 in
Weight	14 lb

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACCC Str Size	BRUSSELS 430mm ²
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - YTW430MMRC15ACK5LS_MODEL-STEP](#)
[3D Models - YTW430MMRC15ACK5LS_MODEL-IGES](#)
[3D Models - YTW430MMRC15ACK5LS_MODEL-PDF](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTW430MMRC15ACK5LS-SPEC-EN | REV 8/2023