



YTW43R43REK, Single Pad Full Tension Deadend for ACSR

By Burndy
Catalog # [YTW43R43REK](#)



Single Pad Full Tension Deadend for ACSR Conductor.

General

Connector Type	Deadend
Die Index	724
Feature - Barrel Style	Tapered
Material	Aluminum
Material - Clevis	Steel
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	NEMA
Physical Attribute - Pad Orientation	15 Degree Angle
UPC	781810517154
UPC 12 Digit	7818105171544

Dimensions

Dimension - B Length inch	2.5 in
Dimension - Bolt Size fraction	1/2
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	520 mm
Dimension - Length Overall inch	20.49 in
Dimension - Pad Width inch	3.25 in

Conductor Related

Conductor - ACSR Str Size	605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil;636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50018010](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTW43R43REK-SPEC-EN | REV 8/2023