



YTW43R43REKHT, Single Pad Full Tension Deadend for ACSS

By Burndy
Catalog # [YTW43R43REKHT](#)



Single Pad Full Tension Compression Deadend for ACSS Conductor.

General

Connector Type	Deadend
Feature - Barrel Style	Tapered
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	781810517161
UPC 12 Digit	7818105171611

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - Bolt Size fraction	1/2
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.88 in
Dimension - Length Overall inch	24.49 in
Dimension - Pad Width inch	3.25 in
Dimension - Width inch	0.69 in

Conductor Related

Conductor - ACSS Str Size	605 (24/7) kcmil;605 (26/7) kcmil;605 (30/7) kcmil;605 (30/19) kcmil;636 (20/7) kcmil;636 (22/7) kcmil;636 (24/7) kcmil;636 (26/7) kcmil;636 (30/7) kcmil;636 (30/19) kcmil;666.6 (24/7) kcmil
Conductor - ACSS Str Size Range	605 (24/7) kcmil-666.6 (24/7) kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50018275](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTW43R43REKHT-SPEC-EN | REV 8/2023