



YTW451RT481REKHT, Full Tension Deadend Kit with Hardware for ACSS EHV

By Burndy
Catalog # [YTW451RT481REKHT](#)



Full Tension, ACSS EHV Deadend Kits, Hardware TMH24, TERN 795 (45/7) kcmil, YTW451RT481REKHTNT Aluminum Dead End Assy., BYNA451RT15HHT Terminal.

Application

For 250 Deg C. rated ACSS transmission lines, Corona free operation up to 230 KV

General

Connector Type	Deadend
Physical Attribute - Number of Holes	4
Prefilled Oxide Inhibitor	N
UPC	781810491164
UPC 12 Digit	7818104911644

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Hole Size inch	1.25 in
Dimension - Length Overall inch	29.41 in
Dimension - Pad Width inch	3.25 in
Dimension - Width inch	0.75 in

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	TERN 795 (45/7) kcmil
Conductor - ACSS Str Size Range	715.5 (30/19) kcmil-795 (45/7) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Sales Drawings - 10085264](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTW451RT481REKHT-SPEC-EN | REV 8/2023