



YTW48RDT481REKHT, Double Pad, EHV Full Tension Deadend for ACSS

By Burndy
Catalog # [YTW48RDT481REKHT](#)



Double Pad, EHV Full Tension Compression Deadend for ACSS Conductor.

General

Connector Type	Deadend
Feature - Barrel Style	Tapered
Material	Aluminum
Physical Attribute - Number of Holes	8
UPC	781810518038
UPC 12 Digit	7818105180388

Dimensions

Dimension - B Length fraction	2-11/16 in
Dimension - B Length inch	2.69 in
Dimension - Bolt Size fraction	1/2
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	29.5 in
Dimension - Pad Width inch	3.25 in
Dimension - Width inch	0.75 in

Conductor Related

Conductor - ACSS Str Size 900 (45/7), 954 (45/7)

Certifications And Compliance

Certification - CSA Approved No
Standards - RoHS Compliance UI
Status

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50020585](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YTW48RDT481REKHT-SPEC-EN | REV 5/2024