



# YTW48RT481REKHT, Full Tension ACSS EHV Deadend Kit with Hardware

By Burndy  
Catalog # [YTW48RT481REKHT](#)



Full Tension, ACSS EHV Deadend Kits, Hardware TMH24, RUDDY 900 (45/7) kcmil, RAIL 954 (45/7) kcmil, YTW48RT481REKHTNT Aluminum Dead End Assy., BYNA49RT15HHT Terminal.

## Application

For 250 Deg C. rated ACSS transmission lines, Corona free operation up to 230 KV

## General

Connector Type	Deadend
Physical Attribute - Number of Holes	4
Prefilled Oxide Inhibitor	N
UPC	781810491140
UPC 12 Digit	7818104911400

## Dimensions

Dimension - B Length inch	2.69 in
Dimension - Hole Size inch	1.25 in
Dimension - Length Overall inch	29.50 in
Dimension - Pad Width inch	3.25 in
Dimension - Width inch	0.75 in

## Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

## Conductor Related

Conductor - ACSS Str Size	900 (45/7) kcmil;900 (54/7) kcmil;954 (42/7) kcmil;954 (20/7) kcmil;954 (45/7) kcmil
Conductor - ACSS Str Size Range	900 (45/7) kcmil - 954 (45/7) kcmil
Conductor - Material	Aluminum

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Sales Drawings - 10085264](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YTW48RT481REKHT-SPEC-EN | REV 8/2023