



YTW49RT483REKHT, Full Tension ACSS EHV Deadend Kit with Hardware

By Burndy
Catalog # [YTW49RT483REKHT](#)



Full Tension, ACSS EHV Deadend Kits, Hardware TMH24, ORTOLAN 1033.5 (45/7) kcmil, YTW49RT483REKHTNT Aluminum Dead End Assy., BYNA49RT15HHT Terminal.

Application

For ACSS Conductor, Corona free operation up to 230 KV

General

Connector Type	Deadend
Feature - Barrel Style	Tapered
Material	Aluminum
Physical Attribute - Number of Holes	4
Prefilled Oxide Inhibitor	N
UPC	781810518250
UPC 12 Digit	7818105182500

Dimensions

Dimension - B Length fraction	2-11/16 in
Dimension - B Length inch	2.69 in
Dimension - Bolt Size fraction	1/2
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	31.35 in
Dimension - Pad Width inch	3.25 in
Dimension - Width inch	1.00 in

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	ORTOLAN 1033.5 (45/7) kcmil
Conductor - ACSS Str Size Range	1033.5 (45/7) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10085264](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTW49RT483REKHT-SPEC-EN | REV 8/2023