



# YTW52RT50REKHTSC, Full Tension ACSS EHV Deadend Kit with Hardware

By Burndy  
Catalog # [YTW52RT50REKHTSC](#)

Full Tension, ACSS EHV Deadend Kits, Hardware TMH22, FINCH 1113 (54/19) kcmil, YTW52RT50REKHTNT Aluminum Dead End Assy., BYNA52RT15HT Terminal, STS44A4NCG2 (Qty.2).



\*Representative Image

## General

Connector Type	Deadend
Physical Attribute - Number of Holes	4
Prefilled Oxide Inhibitor	N
UPC	781810497418
UPC 12 Digit	7818104974188

## Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

## Conductor Related

Conductor - ACSS Str Size	FINCH 1113 (54/19) kcmil
Conductor - Material	Aluminum

## Certifications and Compliance

Standards - RoHS Compliance UI Status

## Logistics

Minimum Pack Quantity 1

## Product Assets

[3D Models - YTW52RT50REKHTSC\\_MODEL-PDF](#)  
[3D Models - YTW52RT50REKHTSC\\_MODEL-IGES](#)  
[3D Models - YTW52RT50REKHTSC\\_MODEL-STEP](#)  
[Sales Drawings - 10085264](#)



A proud member of the Hubbell Family.