



YTW56RT590REKHT, Full Tension ACSS EHV Deadend Kit with Hardware

By Burndy
Catalog # [YTW56RT590REKHT](#)



Full Tension, ACSS EHV Deadend Kits, Hardware TMH9, FALCON 1590 (54/19) kcmil, YTW56RT590REKHTNT Aluminum Dead End Assy., BYNA56RT15HHT Terminal.

Application

For ACSS Conductor, Corona free operation up to 230 KV

General

Connector Type	Deadend
Physical Attribute - Number of Holes	4
Prefilled Oxide Inhibitor	N
UPC	781810490914
UPC 12 Digit	7818104909144

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Hole Size inch	1.25 in
Dimension - Length Overall inch	35.99 in
Dimension - Pad Width inch	4.00 in
Dimension - Width inch	1.00 in

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	FALCON 1590 (54/19) kcmil
Conductor - ACSS Str Size Range	1590 (54/19) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10085264](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTW56RT590REKHT-SPEC-EN | REV 8/2023