



Z3434, Copper - Compression Cone (Mole)

By Burndy
Catalog # [Z3434](#)

Split Cone, 500 Kcmil, 1.26 in L, Tin Plated.

Features

- Split Cone Copper Compression, close tolerances provide maximum secureness in gripping a wide range of cable sizes

Application

For Use With Socket And Nut Assembly: Z34NR And 34NRB

General

Catalog Number	Z3434
Connector Type	Cone
EU RoHS Indicator	Yes
Material	Brass
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	MOLE
Type	Z-MOLE
UPC	781810017425
UPC 14 Digit GTIN	00781810017425

Dimensions

Dimension - Length Overall	126
inch	
Length	1.26 in

Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	23200

Product Assets

[Catalogs - BURNDY Master Catalog - Section K - Underground](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_Z_LineArt](#)
[Sales Drawings - 50015027](#)
[Specifications - Z3434](#)



A Hubbell brand