



Z34NRB, Copper - Socket And Nut Assembly (Mole)

By Burndy
Catalog # [Z34NRB](#)



Socket & Nut Assembly, 500 kcmil, 7/8" - 14 Stud.

General

Connector Type	Nut
Installation Torque Recommended in-lb	700 lb-in
Insulation Type	Rubber
Material	Bronze Alloy, Leaded
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810017470
UPC 12 Digit	7818100174700

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - Cross Flats inch	1.50 in
Dimension - Length Overall inch	1.5
Dimension - Width inch	2.13 in
Weight	0.74 lb

Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	2088

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50032378](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-Z34NRB-SPEC-EN | REV 8/2023