



1PBS350, UV Rated Black Splicer/Reducer, 2, #10-350 kcmil

By Burndy
Catalog # 1PBS350



UV Rated Black UNITAP™, 2, #10 - 350 Kcmil, 4.63 in L, 1.34 in W.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

General

Application	For Indoor Use Only, Copper Or Stranded Aluminum
Catalog Number	1PBS350
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	5/16
Installation Torque	275 in-lb
Recommended in-lb	
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	2
Physical Attribute - Number of	2
Screws	
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194° F
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810295908
UPC 12 Digit	7818102959088

Dimensions

Dimension - Height inch	2.35 in
Dimension - L Length Overall mm	118 mm
Dimension - Length Overall inch	4.63 in
Dimension - Screw Size inch	5/16
Dimension - Width fraction	1-17/50 in
Dimension - Width inch	1.34 in
Dimension - Width mm	34 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil
Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	10 AWG - 350 kcmil
Conductor Size	10 AWG-350 KCMIL
Conductor Type	AL C Str-Size CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct	No
Burial	
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_PBS_LineArt](#)
- [Sales Drawings - SD214514-03](#)



A Hubbell brand