



## 1PL43, UV Rated Black, 1-sided, 3-port, #14-4 AWG

By Burndy  
Catalog # [1PL43](#)

UV Rated Black Unitap, 3, #14 - 4, 1.59 in L, 1.25 in W, Range-taking capability reduces the number of connectors carried in inventory.



### Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

### General

Application	For Indoor Use Only, Copper Or Stranded Aluminum
Catalog Number	1PL43
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	1/8
Installation Torque	45 in-lb
Recommended in-lb	
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	3
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194° F
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810286975
UPC 12 Digit	7818102869755

### Dimensions

Dimension - Height fraction	1.25 in
Dimension - Height inch	1.25 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.51 in
Dimension - Screw Size inch	1/4
Dimension - Width fraction	1-1/4 in
Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - AL Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - AL Str Size Range	14 AWG - 4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG - 4 AWG
Conductor Size	14-4 AWG
Conductor Type	AL C Str-Size CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct	No
Burial	
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Product Assets

[3D Models - 1PL43\\_MODEL-STEP](#)

[3D Models - 1PL43\\_MODEL-IGES](#)

[3D Models - 1PL43\\_MODEL-PDF](#)

[Catalogs - UNITAP™ Products](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR\\_PL\\_LineArt](#)

[Sales Drawings - SD214514-08](#)



A Hubbell brand