



# 1PLD7503HD, UV Rated Black, 2-sided, 3-port, #2 AWG-750 kcmil

By Burndy  
Catalog # [1PLD7503HD](#)



750-2 TWO-SIDED 3 PORT HD BLK.

## Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

## General

Catalog Number	1PLD7503HD
Connector Type	Multi Tap
Hex Key	3/8 in
Installation Torque	500 in-lb
Recommended in-lb	
Material	Aluminum
Number Of Ports	3
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480735

## Dimensions

Dimension - L Length Overall mm	101.6
Dimension - Length Overall inch	4

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor Size	2 AWG-750 KCMIL
----------------	-----------------

## Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50079815](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-1PLD7503HD-SPEC-EN | REV 6/2024