

25CHENBOX, 1/4" Silicon Bronze Hex Nut

By Burndy
Catalog # [25CHENBOX](#)



Silicon Bronze, 1/4-20 Thread Size, Hexagonal nuts.

General

Application	Used to fasten the joints
Catalog Number	25CHENBOX
Connector Type	Nut
EU RoHS Indicator	Yes
Installation Torque	80 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Sub Brand	DURIUM
Trade Name	DURIUM™
Type	HARDWARE
UPC	781810012420
UPC 12 Digit	7818100124200

Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25 in
Dimension - Outside Diameter inch	0.44 in
Dimension - Thread Size	1/4 - 20
Dimension - Threads per inch	20

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [3D Models - 25CHENBOX_MODEL-STEP](#)
- [3D Models - 25CHENBOX_MODEL-IGES](#)
- [3D Models - 25CHENBOX_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_38CHENBOX_LineArt](#)
- [Sales Drawings - wsc206494-01](#)

