



50X250OSBBOX, 1/2" x 2-1/2" Oval Shank Bolt

By Burndy
Catalog # [50X250OSBBOX](#)



1/2 x 2.50 Oval Shank Bolt.

General

Catalog Number	50X250OSBBOX
Connector Type	Bolt - Oval Shank
Installation Torque	480 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
UPC	781810362044
UPC 12 Digit	7818103620444

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.5 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)