



75X125HGSB, 3/4" x 1-1/4" Hex Bolt, Galvanized Steel



By Burndy
Catalog # [75X125HGSB](#)

3/4 x 1.25 Galvanized Steel Hex Bolt.

Features

- Galvanized steel hardware (bolts, nuts, flatwashers and internal tooth lockwashers) are manufactured per ASTM307 Grade A
- Nut surfaces and bolt heads have American Standard dimensions
- Galvanizing is per ASTM A153

General

Catalog Number	75X125HGSB
Connector Type	Galvanized Steel Hex Bolt
Material	GALVANIZED STEEL
UPC	781810283189

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Bolt Size fraction	3/4
Dimension - Bolt Size inch	0.75 in

Dimension - Length Overall	1.25 in
Dimension - Thread Size	3/4-10
Dimension - Threads per inch	11

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	NC
Status	
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - 75X125HGSB Specification Sheet English](#)
[Specifications - 75X125HGSB Specification Sheet French](#)



A Hubbell brand