



# ACC-ECTB68, Horizontal 180 Degree Edge Clip with Nylon6/6 Cable Tie, 8"

By Burndy  
Catalog # ACC-ECTB68

Wiley Edge Clip with Cable Tie, Horizontal (180 Deg.) perpendicular installation.



## General

Application	For routing cable bundles without requiring mounting holes or additional hardware, Available in Nylon 6/6 or Nylon 12 for either horizontal/perpendicular (90°) or vertical/ parallel (180°) styles  50 lb tensile strength, Steel lances securely anchor clips to module frames / purlins, 3 standard cable tie lengths (8", 11", 14") encompass maximum bundle diameters of 1.95" to 3.94"  Custom lengths available
Catalog Number	ACC-ECTB68
Installation Type	Horizontal (180 Deg.) perpendicular installation
Material	Nylon 6/6
Tensile Strength	50 lb.
UPC	621945554375

## Dimensions

Dimension - Bundle Diameter	1.95 in
Max inch	
Length	8 in

## Certifications And Compliance

Certification - CSA Approved	N
Certification - cULus	N
Certified Listed	UL62275 Recognized
Industry Standard(s)	UL62275 Recognized

## Logistics

Carton Quantity	1000
-----------------	------

## Product Assets

- [Catalogs - Wiley Wire Management Guide](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Certifications - UL Certificate of Compliance UL 62275](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50100741](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-ACCCTB68-SPEC-EN | REV 6/2024