

ACC-F1-270, Stainless Steel Wire Management Clip, Dual Degree, 1 PV Wires, Module



By Burndy
Catalog # [ACC-F1-270](#)

90 Degree Module Cable Clip.

Features

- Accommodates a broad range of cable combinations and sizes
- Environmentally tested (UL2703 and ASTM B117)
- No tools required for installation
- Coined and rolled edges to prevent damage to cable insulation

Application

1 to 2 PV wires, Micro Inverter Trunk or AC cables
Wire Diameter Range: Max 13.0mm in total

General

Catalog Number	ACC-F1-270
Item Type	3B
Material	304 Stainless Steel
Mounting Method	Module Frame or Flange Clip - 90 Degree & Straight on
	Flange Thickness Range: 1.0mm - 3.0 mm
Type	Cable Clips
UPC	621945452602
UPC 14 Digit GTIN	00621945452602

Dimensions

Dimension - Thread Size	-
-------------------------	---

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	4000
-----------------	------

Product Assets

- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - Wiley Wire Management Guide](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Certifications - UL Certificate of Compliance, UL 1565, CSA C22.2 No. 18.5-13](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50059623](#)
- [Specifications - ACC-F1-270 Specification Sheet French](#)
- [Specifications - ACC-F1-270 CUTSHEET 01282016](#)
- [Specifications - ACCF1270 Specification Sheet English](#)