



ACC-F4-90-1, Stainless Steel Wire Management Clip, Dual Degree, 1 to 4 PV Wires, Module



By Burndy
Catalog # [ACC-F4-90-1](#)

90 Degree Module Cable Clip.

Features

- Accommodates a broad range of cable combinations and sizes
- Environmentally tested (UL2703 and ASTM B117)
- No tools required for installation
- Coined and rolled edges to prevent damage to cable insulation

Application

1 to 4 PV cables
Wire Diameter Range: 4.1mm - 6.7mm per each cable

General

Catalog Number	ACC-F4-90-1
Item Type	3B
Material	304 Stainless Steel
Mounting Method	Module Frame or Flange Clip - 90 Degree & Straight on Flange Thickness Range: 1.3mm - 2.5 mm
Trade Name	WILEY
Type	Cable Clips
UPC	781810671351
UPC 14 Digit GTIN	00781810671351

Dimensions

Dimension - Length Overall	1.36 in
inch	

Dimension - Thread Size -

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	4000
-----------------	------

Product Assets

- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - Wiley Wire Management Guide](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50042750](#)
- [Specifications - ACC-F4-90-1 Specification Sheet French](#)
- [Specifications - ACC-F4-90-1,Wiley](#)
- [Specifications - ACCF4901 Specification Sheet English](#)
- [Video - Wiley Dual Mounting Clips](#)