

ACC-FBC, Stainless Steel Wire Management Clip, Dual Degree, Cable Tie Mounting Base, Module



By Burndy
Catalog # [ACC-FBC](#)

Module Cable Clip Mounting Base.

Features

- 304 Stainless Steel Clip for affixing cables ties to a module flange

Application

Bundles of PV wire, Micro Inverter Trunk or AC cable
Max Cable Tie Width: 8.0mm

General

Catalog Number	ACC-FBC
Item Type	3B
Material	304 Stainless Steel
Mounting Method	Module Cable Tie Mounting Base - 90 Degree & Straight on Flange Thickness Range: 1.3mm - 3.0mm
Trade Name	WILEY
Type	Cable Clips
UPC	781810670170
UPC 14 Digit GTIN	00781810670170

Dimensions

Dimension - Thread Size -

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	N
Certification - UL Recognized	N
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	8000
-----------------	------

Product Assets

- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - Wiley Wire Management Guide](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Certifications - UL Certificate of Compliance CAN/CSA-C22.2 No. 62275-10](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50037678](#)
- [Specifications - ACCFBC Specification Sheet English](#)
- [Specifications - ACC-FBC Specification Sheet French](#)
- [Specifications - ACC-FBC](#)