



# ACC-FPV90, Stainless Steel, 90 degree, 2 wire Module Cable Clip

By Burndy  
Catalog # ACC-FPV90

2 wire Module Cable Clip 90 Degree

### Features

- Accommodates a broad range of cable combinations and sizes
- Environmentally tested (UL2703 and ASTM B117)
- No tools required for installation
- Coined and rolled edges to prevent damage to cable insulation

### Application

1 to 2 PV cables, Wire Diameter Range: 5.0mm - 8.0mm per each cable

### General

Catalog Number	ACC-FPV90
Construction Material - Main	304 STAINLESS STEEL
EU RoHS Indicator	Under Review
Material	304 Stainless Steel
Mounting Method	Module Frame or Flange Clip - 90 Degree, Flange Thickness Range: 1.0mm - 3.0mm
Type	Cable clip
UPC	621945514508

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
UL Listed	Yes

### Product Assets

- Catalogs - [Burndy Grounding Catalog](#)
- Catalogs - [BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- Catalogs - [Wiley Wire Management Guide](#)
- Catalogs - [BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- Catalogs - [BURNDY Master Catalog - Section G - Wire Management](#)
- Certifications - [UL Certificate of Compliance, UL 1565, CSA C22.2 No. 18.5-13](#)
- Sales Drawings - [50084791](#)
- Specifications - [Burndy\\_ACC-FPV90\\_Specsheet](#)
- Specifications - [ACC-FPV90 Specification Sheet French](#)
- Specifications - [ACCFPV90 Specification Sheet English](#)
- Video - [Wiley 90 Degree Module Clips](#)
- Video - [Wiley 90 Degree Module Clips](#)



A Hubbell brand