



ACC-R2, Rail Cable Clip, 1 wire Max 0.55"; 2 wire Max 0.43"

By Burndy
Catalog # ACC-R2

Rail Cable Clips.

Features

- 304 Stainless Steel Clips that install on the rail, channel, or slot

Application

1 to 2 PV wires, Micro Inverter Trunk or AC cables
Wire Diameter Range: 4.1mm - 8.0mm per each cable (2 cables)4.1mm - 14.0mm per each cable (1 cable)

General

Catalog Number	ACC-R2
Item Type	3B
Material	304 Stainless Steel
Mounting Method	Racking: Unirac, Ironrigde, Everest or similar rack profiles
Trade Name	WILEY
Type	Cable Clips
UPC	781810537084
UPC 14 Digit GTIN	00781810537084

Dimensions

Dimension - Thread Size -

Certifications And Compliance

Certification - CSA Approved Yes

Certification - ETL	N
Certification - UL Recognized	N
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity 4000

Product Assets

- Catalogs - Burndy Grounding Catalog
- Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding
- Catalogs - Wiley Wire Management Guide
- Catalogs - BURNDY Master Catalog - Section G - Wire Management
- Certifications - UL Certificate of Compliance, UL 1565, CSA C22.2 No. 18.5-13
- Customer Notices - Prop 65 Notice
- Sales Drawings - 30023999
- Specifications - ACC-R2
- Specifications - ACC-R2 Specification Sheet French
- Specifications - ACCR2 Specification Sheet English