



# ACC-R4, Rail Cable Clip, Up to 4 0.29" PV wires

By Burndy  
Catalog # ACC-R4

Rail Cable Clips.

## Features

- 304 Stainless Steel Clips that install on the rail, channel, or slot

## Application

1 to 4 PV wires, Wire Diameter Range: 4.1mm - 6.5mm per each cable

## General

Catalog Number	ACC-R4
Construction Material - Main	Nylon
EU RoHS Indicator	Contact Manufacturer
Item Type	3B
Material	304 Stainless Steel
Mounting Method	Racking: Unirac, Ironrigde, Everest or similar rack profiles
Trade Name	WILEY
Type	Cable Clips
UPC	781810537091
UPC 14 Digit GTIN	00781810537091

## Dimensions

Dimension - Thread Size -

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	N
Certification - UL Recognized	N
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	4000
-----------------	------

## Product Assets

- Catalogs - Burndy Grounding Catalog
- Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding
- Catalogs - Wiley Wire Management Guide
- Catalogs - BURNDY Master Catalog - Section G - Wire Management
- Customer Notices - Prop 65 Notice
- Sales Drawings - 30023996
- Specifications - ACC-R4 Specification Sheet French
- Specifications - ACC-R4
- Specifications - ACCR4 Specification Sheet English