

AYPO1000, Compression Pin Adapter, 1000 kcmil, .81" Pin Dia, AL9CU

By Burndy
Catalog # [AYPO1000](#)

Aluminum compression adaptor, UL Listed 90° C, Up to 35 kV, Cover is rated for 600 V.

Application

Wire Termination

General

Catalog Number	AYPO1000
Color Code	Brown
Connector Type	OFFSET PIN
Die Index	302
Finish Type	Tin-Plated
Material	ALUMINUM
Pin Type	Solid
Terminal Type	Pin
Trade Name	HYPLUG™
Type	Aluminum Pin Adapters
UPC	621945586444

Dimensions

Equivalent Pin Size	500 kcmil
Length	1.76 in

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - AL Str Size	1000 KCMIL
Conductor - AL Str Size Range	1000 kcmil
Conductor - Copper DLO Size	777 DLO



Conductor - Copper DLO Size Range	777 kcmil
Conductor - Copper Str Compact Size	1000 KCMIL
Conductor - Copper Str Size	1000 KCMIL
Conductor - Copper Str Size Range	1000 kcmil
Conductor - Material	ALUMINUM / COPPER
Conductor Size	1000 KCMIL
Conductor Type	CODE/FLEX
Wire Size	1000 KCMIL

Certifications And Compliance

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
UL Listed	Yes

Logistics

Carton Quantity	6
Pallet Quantity	1776

Product Assets

- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50103891](#)
- [Specifications - AYPO1000 Specification Sheet French](#)
- [Specifications - AYPO1000 Specification Sheet English](#)