

B22G244N Flexible Copper Braid

By Burndy

Catalog # [B22G244N](#)

Flexible Copper Braid.



General

Catalog Number	B22G244N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810142912

Dimensions

Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Length	24 in

Electrical Ratings

Amperage Rating	1300 A
Rating - Outdoor Amperage	1300

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - 10095071](#)



A Hubbell brand