



B232, Horizontal Cable Tap to Horizontal Cable Run, 2/0 AWG (Run & Tap)

By Burndy
Catalog # [B232](#)

Mold, Horizontal Cable Tap to Horizontal Cable Run, 2/0 AWG (Run & Tap), 90 Weld Metal.

Application

For Joining Horizontal Cable Tap To A Horizontal Run Cable

General

Catalog Number	B232
EU RoHS Indicator	Yes
Sub Brand	BURNDYWELD
Trade Name	BURNDYWeld®
UPC	781810378397
UPC 14 Digit GTIN	00781810378397

Conductor Related

Conductor - Copper Str Run	2/0 AWG
Conductor - Copper Str Tap	2/0 AWG
Conductor Type	• CU C Str-Run • CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1
Pallet Quantity	480

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BCC-2_LineArt](#)
- [Sales Drawings - 10044340](#)
- [Specifications - B232 Specification Sheet English](#)
- [Specifications - B232 Specification Sheet French](#)