



B2D19D42NTNCG1 Flexible Copper Braid

By Burndy

Catalog # [B2D19D42NTNCG1](#)

Tin Plated Ferrules.



General

Catalog Number	B2D19D42NTNCG1
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810421017
UPC 12 Digit	7818104210177

Dimensions

Dimension - L Length Overall mm	493 mm
Dimension - Length Overall inch	19.39 in
Dimension - Pad Width inch	0.94
Length	19.4 in
Weight	1.06 lb

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	395

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

- [3D Models - B2D19D42NTNCG1_MODEL-PDF](#)
- [3D Models - B2D19D42NTNCG1_MODEL-STEP](#)
- [3D Models - B2D19D42NTNCG1_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - cWSC34887](#)



A Hubbell brand