



## BA10E38, Vinyl Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # [BA10E38](#)

Cu Terminal, Bulk, Ring Tongue, #12 - #10 AWG Str, 600 V, 3/8" stud, Polyvinylchloride Insulated, Yellow.



### Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

### General

Application	For Commercial, Light Duty Industrial Control and Power Circuit Applications
Catalog Number	BA10E38
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810026489
UPC 12 Digit	7818100264899

### Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Hole Size fraction	16/41
Dimension - Hole Size inch	0.39 in
Dimension - Length Overall inch	1.27 in
Dimension - Pad Width inch	0.53 in
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.45 in

### Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	500
Pallet Quantity	99999

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_BA16E6\\_LineArt](#)  
[Sales Drawings - 50093722](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-BA10E38-SPEC-EN | REV 6/2024