

BA14EF10, Vinyl Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [BA14EF10](#)



Copper Terminal, Fork Tongue, 16-14 AWG, #8-#10 Stud, Vinyl Insulated.

General

Application	
Catalog Number	BA14EF10
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	
UPC	781810026663
UPC 12 Digit	7818100266633

Dimensions

Dimension - Bolt Size fraction	#10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.41 in
Dimension - Stud Size inch	#10
Dimension - Z (inch)	0.31 in

Conductor Related

Conductor - Copper Solid Size Range	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size Range	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BA14EF10_LineArt](#)
- [Sales Drawings - 50094171](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-BA14EF10-SPEC-EN | REV 6/2024