

BA14EF2, Vinyl Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [BA14EF2](#)



Polyvinylchloride Insulated Copper Fork Terminal, Stud size:2, Wire strip length:13/64".

General

Application	For Commercial And Light Duty Industrial Control And Power Circuit Applications
Catalog Number	BA14EF2
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	BA-EF
UPC	781810026434
UPC 12 Digit	7818100264344

Dimensions

Dimension - Bolt Size fraction	#2
Dimension - Hole Size fraction	1/11
Dimension - Hole Size inch	0.09 in
Dimension - Length Overall inch	0.75 in
Dimension - Pad Width inch	0.17 in
Dimension - Stud Size inch	#2
Dimension - Z (inch)	0.23 in

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BA14EF10_LineArt](#)
- [Sales Drawings - 50094171](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-BA14EF2-SPEC-EN | REV 6/2024