



BBB14224B, Bare Copper Busbar, 24" Long, 36 Holes

By Burndy
Catalog # [BBB14224B](#)



Copper Busbar, 36 Holes, 24 in L, Can be used as a common ground point and power applications.

General

Application	For Used As A Common Ground Point And Power Applications
Catalog Number	BBB14224B
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Holes	36
Sub Brand	BUS BAR
Type	BBB
UPC	781810489321
UPC 12 Digit	7818104893211

Dimensions

Dimension - Bar Length inch	24 in
Dimension - Bar Length mm	610 mm
Dimension - Bar Thickness inch	0.25 in
Dimension - Bar Thickness mm	6 mm
Dimension - Bar Width inch	2 in
Dimension - Bar Width mm	51 mm
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - Width fraction	2 in
Dimension - Width inch	2.00 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1
Pallet Quantity	90

Product Assets

- [Brochures - Grounding Busbars - Complete Product Guide](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10103867](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-BBB14224B-SPEC-EN | REV 6/2024