



BD102N Flexible Copper Braid

By Burndy
Catalog # [BD102N](#)

Flexible Copper Braid 102 inches long.



General

Catalog Number	BD102N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810374719
UPC 12 Digit	7818103747199

Dimensions

Dimension - L Length Overall mm	2591 mm
Dimension - Length Overall inch	102 in
Length	102 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10045735-01_D](#)



A Hubbell brand