

BE12N1 Flexible Copper Braid

By Burndy
Catalog # [BE12N1](#)

Flexible Copper Braid.



General

Catalog Number	BE12N1
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810490822
UPC 12 Digit	7818104908222

Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Length	12 in

Electrical Ratings

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10105628](#)