



## BE12U Flexible Copper Braid

By Burndy  
Catalog # [BE12U](#)

Cu Flexible Braid, Undrilled, 12.00" L, Amp Rating: 340 Indoor, 405 Outdoor.



### General

Catalog Number	BE12U
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810202593
UPC 12 Digit	7818102025933

### Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Length	12 in

### Electrical Ratings

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_BD\\_Lineart](#)  
[Sales Drawings - 10106290](#)



A Hubbell brand