



BF18N Flexible Copper Braid

By Burndy
Catalog # [BF18N](#)

Cu Flexible Braid Jumper, 2 NEMA Holes 2 Ferrules, 1.75" Spacing, 18.00" L, .56" Hole Dia., Amp Rating: 360(Indoor) 430(Outdoor).



General

Catalog Number	BF18N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810005255
UPC 12 Digit	7818100052555

Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.19 in
Length	18 in

Electrical Ratings

Rating - Indoor Amperage	360
Rating - Outdoor Amperage	430

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BD_Lineart](#)
- [Sales Drawings - SE..210201-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-BF18N-SPEC-EN | REV 6/2024