

BIBD6006MT, Double Sided Mounted Six Conductor Clear Insulated Mult-Tap Connector

By Burndy

Catalog # [BIBD6006MT](#)



Mounting Version Multi-Port; Double-Sided Entry.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

General

Catalog Number	BIBD6006MT
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/8
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	6
Physical Attribute - Number of Screws	8
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD-MT
UPC	781810253410
UPC 14 Digit GTIN	00781810253410

Dimensions

Dimension - Height fraction	2.875 in
Dimension - Height inch	2.88 in
Dimension - Height mm	73.2 mm
Dimension - L Length Overall mm	264 mm
Dimension - Length Overall inch	10.41 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Electrical Ratings

Amperage Rating	780 A
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Size Range	4 AWG - 600 kcmil
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil
Conductor - Copper Str Size Range	4 AWG - 600 kcmil
Conductor Size	4 AWG-600 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

[Catalogs - UNITAP™ Products](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BIBD-MT_LineArt](#)

[Sales Drawings - SD213079-02_B](#)
[Specifications - BIBD6006MT Specification Sheet English](#)
[Specifications - BIBD6006MT Specification Sheet French](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY_CA-BIBD6006MT-SPEC-EN | REV 4/2025