

BIBD75012, Double Sided Twelve Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBD75012](#)



Plastisol covered multiple tap Connector with Double-Sided Entry. WIRE RANGE: #2 AWG - 750 kcmil AL/CU.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

General

Application	Tap connections are made quickly and easily with the UNITAP line of connectors. UL486B Listed. Dual-rated AL9CU for any stranded copper or stranded aluminum applications.
Catalog Number	BIBD75012
Color	
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/8
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	12
Physical Attribute - Number of Screws	12
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD
UPC	781810232910
UPC 12 Digit	7818102329100

Dimensions

Dimension - Height fraction	3 in
Dimension - Height inch	3.00 in
Dimension - L Length Overall mm	422 mm
Dimension - Length Overall inch	16.63 in
Dimension - Width fraction	3-19/50 in
Dimension - Width inch	3.38 in
Dimension - Width mm	86 mm
Dimensions	16.63 in x 3.38 in x 3 in
Height	3 in
Length	16.63 in
Width	3.38 in

Electrical Ratings

Voltage - Maximum	600 V
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil
Conductor - AL Str Size Range	2 AWG-750 kcmil
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Size Range	2 AWG-750 kcmil
Conductor Size	2 AWG-750 KCMIL
Conductor Type	AL C Str-Size CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct	No
Burial	
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BIBD_Lineart](#)
[Sales Drawings - sc210991-09](#)



A Hubbell brand