

# BIBS3504DB, Direct Burial Submersible Four Conductor Insulated Multi-Tap Connector

By Burndy  
Catalog # [BIBS3504DB](#)



Direct Burial UNITAP™, 350 Kcmil -12 AWG Str., 5.03 in L,  
Designed specifically for direct burial applications.

## Features

- Supplied with aluminum set-screws
- Supplied with oxide inhibitor pre-installed
- Submersible rated and suitable for Direct Burial

## General

Application	For Outside Direct Burial
Catalog Number	BIBS3504DB
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Installation Torque	450 LBS/in
Recommended in-lb	
Insulation	Y
Material	Aluminum
Number Of Ports	4
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port - Direct Burial
UPC	781810523605
UPC 12 Digit	7818105236055

## Dimensions

Dimension - Height inch	2.46 in
Dimension - L Length Overall mm	128 mm
Dimension - Length Overall inch	5.03 in
Dimension - Strip Length inch	1.125
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - AL Str Size Range	12 AWG - 350 kcmil
Conductor - Copper Str Size Range	12 AWG - 350 kcmil
Conductor Size	12 AWG-350 KCMIL
Conductor Type	AL C Str-Size
	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Product Assets

[Catalogs - UNITAP™ Products](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_BIBS\\_Lineart](#)  
[Sales Drawings - 30013013](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-BIBS3504DB-SPEC-EN | REV 6/2024