



BIBS3505DB, Direct Burial Submersible Five Conductor Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBS3505DB](#)



Multi Port Direct Burial, 5 Ports, 350 kcmil-12 AWG Str, 600 V.

Features

- Supplied with aluminum set-screws
- Supplied with oxide inhibitor pre-installed
- Submersible rated and suitable for Direct Burial

General

Application	For Outside Direct Burial
Catalog Number	BIBS3505DB
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Installation Torque	450 LBS/in
Recommended in-lb	
Insulation	Y
Material	Aluminum
Number Of Ports	5
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port - Direct Burial
UPC	781810523612
UPC 12 Digit	7818105236122

Dimensions

Dimension - Height inch	2.46 in
Dimension - L Length Overall mm	158 mm
Dimension - Length Overall inch	6.24 in
Dimension - Strip Length inch	1.125
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size Range	12 AWG - 350 kcmil
Conductor - Copper Str Size Range	12 AWG - 350 kcmil
Conductor Size	12 AWG-350 KC MIL
Conductor Type	AL C Str-Size
	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BIBS_Lineart](#)
- [Sales Drawings - 30013013](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-BIBS3505DB-SPEC-EN | REV 6/2024