

## BITO750FX, Aluminum Multi-tap, Opposite Side Entry, #2 AWG-750 kcmil, 2 Port



By Burndy  
Catalog # [BITO750FX](#)

Aluminum UNITAP, Tap - Opposite Side Entry, #2 AWG-750  
Kcmil, 2 PORT

### General

|                    |                |
|--------------------|----------------|
| Catalog Number     | BITO750FX      |
| Hex Key            | 3/8 in         |
| Insulation         | Y              |
| Material           | Aluminum       |
| Number Of Ports    | 2              |
| Plated             | Y              |
| Plating Type       | Tin Plated     |
| Temperature Rating | 135°C          |
| Trade Name         | UNITAP™        |
| UPC                | 621945440692   |
| UPC 14 Digit GTIN  | 00621945440692 |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - Height inch         | 3.00 in  |
| Dimension - Height mm           | 76.00 mm |
| Dimension - L Length Overall mm | 73.15 mm |
| Dimension - Length Overall inch | 2.88 in  |
| Dimension - Width inch          | 2.75 in  |
| Dimension - Width mm            | 69.85 mm |

### Electrical Ratings

|                   |       |
|-------------------|-------|
| Operating Voltage | 600 V |
| Voltage - Maximum | 600 V |

### Conductor Related

|                               |                    |
|-------------------------------|--------------------|
| Conductor - AL Str Size Range | 2 str. - 750 kcmil |
|-------------------------------|--------------------|

|                                      |                                                                                                                  |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper DLO Size Range    | 2 str. - 535 kcmil                                                                                               |
| Conductor - Copper Flex G Size Range | 2 str. - 535 kcmil                                                                                               |
| Conductor - Copper Flex H Size Range | 2 str. - 535 kcmil                                                                                               |
| Conductor - Copper Flex I Size Range | 2 str. - 535 kcmil                                                                                               |
| Conductor - Copper Flex K Size Range | 2 str. - 535 kcmil                                                                                               |
| Conductor - Copper Str Size Range    | 2 str. - 750 kcmil                                                                                               |
| Conductor Type                       | <ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li><li>• CU C Flex-Size</li></ul> |

### Certifications And Compliance

|                                    |              |
|------------------------------------|--------------|
| Certification - CSA Approved       | No           |
| Industry Standard(s)               | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM           |

### Product Assets

[Catalogs - UNITAP™ Products](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50046931](#)  
[Specifications - BITO750FX Specification Sheet French](#)  
[Specifications - BITO750FX Specification Sheet English](#)  
[Specifications - BURNDY\\_BITO750FX\\_Specsheet](#)