



C11CSLH12, Cast Bronze Clamp with Copper Strap, Cable to Water Pipe or Rebar

By Burndy
Catalog # [C11CSLH12](#)



Cast Bronze Ground Clamp w/Cu Strap, 1/2"-1" Water Pipe, #4-#6 Rebar(Main), 1/2" Hub, 2/0-#10 Ground, Zinc Plated H/W.

General

Catalog Number	C11CSLH12
Material	Bronze Alloy
Material - Hardware Plated	Zinc Plated Steel N
Plating Type	Zinc
UPC	781810358658
UPC 12 Digit	7818103586588

Dimensions

Dimension - D inch	6.12 in
Dimension - Height inch	1.75 in
Dimension - L Length Overall mm	216 mm
Dimension - Length Overall inch	8.50 in
Dimension - Pad Width inch	1.06 in
Dimension - Width inch	1.18 in
Dimension - Width mm	30 mm

Conductor Related

Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Str Size Range	10 AWG - 2/0 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10039115-01_C](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-C11CSLH12-SPEC-EN | REV 6/2024