

# C11JA, Cast Bronze Clamp, Armored Cable to Water Pipe

By Burndy  
Catalog # [C11JA](#)

Cast Bronze Clamp, Armored Cable to Water Pipe, 10 AWG - 6 AWG, 1/2" - 1" Water Pipe.



## General

Catalog Number	C11JA
Material	Bronze Alloy
Material - Hardware Plated	Zinc Plated Steel N
Plating Type	Unplated
UPC	781810142110
UPC 12 Digit	7818101421100

## Dimensions

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	77 mm
Dimension - Length Overall inch	3.05 in
Dimension - Width inch	1.41 in
Dimension - Width mm	36 mm

## Conductor Related

Conductor - Armored Cable Size	Y
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG
Conductor - Copper Str Size Range	8 AWG - 6 AWG
Conductor - Pipe EMT Size	3/8 in;1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2in -1 in
Conductor Type	Pipe EMT-Size CU C Solid-Size CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CJA\\_LineArt](#)  
[Sales Drawings - SC210668-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-C11JA-SPEC-EN | REV 6/2024