



CCDFR, Clear Cover, Flame retardant cover for YH292C or YHYH298C, 250 kcmil H-Tap

By Burndy
Catalog # [CCDFR](#)

Clear Polycarbonate H-Tap-Flame Retardant Cover, 250kcmil, 600V.



Application

Cover

General

Catalog Number	CCDFR
Color	
Color Code	Purple
Connector Type	H-TAP COVERS CLEAR
EU RoHS Indicator	Yes
Fire Resistance	Yes
Material	POLYCARBONATE
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Temperature Rating	194
Type	H-Tap Connector
UPC	781810438152
UPC 12 Digit	7818104381522

Dimensions

Dimension - Height inch	1.82 in
Dimension - L Length Overall mm	129 mm
Dimension - Length Overall inch	5.06 in
Dimension - Maximum Conductor Size Accommodated	250 kcmil
Dimension - Width inch	1.48 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size	250 KCMIL
Conductor - Copper Str Compact Size	250 KCMIL
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	COPPER
Conductor - Max Length	0.95 in
Conductor Type	CODE/FLEX
Wire Size	250 KCMIL

Certifications And Compliance

Certification - 94V0 Rated	Y
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Pallet Quantity	2250

Product Assets

[3D Models - CCDFR_MODEL-PDF](#)
[3D Models - CCDFR_MODEL-IGES](#)
[3D Models - CCDFR_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_CCFOFR_LineArt](#)
[Sales Drawings - 10064550](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-CCDFR-SPEC-EN | REV 6/2024

