



CFBGFR Black Cover, Flame retardant cover for YH8C8C or YH6C6C, #8-#6 AWG H-Tap

By Burndy
Catalog # CFBGFR



H-Tap Crimpit cover , Flame retardent.

Application

Cover

General

Catalog Number	CFBGFR
Color	
Color Code	Green
Connector Type	H-TAP COVERS BLACK
EU RoHS Indicator	Yes
Insulation	Y
Material	POLYCARBONATE
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	CF-FR, Flame Retardant
UPC	781810068830
UPC 12 Digit	7818100688300

Dimensions

Dimension - Height inch	1.16 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Width inch	1.24 in
Thickness	0.08 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size	8 AWG-6 AWG
Conductor - Copper Str Compact Size	8 AWG-6 AWG
Conductor - Copper Str Size	8 AWG-6 AWG
Conductor - Copper Str Size Range	#8 AWG-#6 AWG
Conductor - Material	COPPER
Conductor - Max Length	0.65 in
Conductor Type	CODE/FLEX
Wire Size	8 AWG-6 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	14400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_CFO_LineArt](#)
[Sales Drawings - SD208803-01_1](#)



A proud member of the Hubbell Family.