



CL501TNMHWSS, Copper Lay-in Lug, Stainless Steel Tongue, Mounting Hardware Included

By Burndy
Catalog # [CL501TNMHWSS](#)



LAY-IN LUG W/SS MOUNTING HDWR DIRECT BURIAL LUG
cULus WIRE RANGE: #14-#4 Cu QUANTITY: 10 PIECES PER BAG.

Features

- Open-faced design allows for fast lay-in of conductor without the need for cutting or breaking
- Stainless steel screws used for excellent corrosion resistance

General

Catalog Number	CL501TNMHWSS
Material	Copper
Material - Hardware	Stainless Steel
Plated	Y
Plating Type	Tin
Trade Name	QIKLUG™
UPC	781810478769
UPC 12 Digit	7818104787699

Dimensions

Dimension - D inch	0.47 in
Dimension - Height inch	0.85 in
Dimension - Hole Size inch	0.22 in
Dimension - Hole Size mm	6 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.13 in
Dimension - N inch	0.19 in
Dimension - Stud Size inch	17/64
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm

Conductor Related

Conductor - Copper Str Size	14;13;12;11;10;9;8;7;6;5;4
Conductor - Copper Str Size Range	14 AWG - 4 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500
-----------------	-----

Product Assets

- [3D Models - CL501TNMHWSS_MODEL-IGES](#)
- [3D Models - CL501TNMHWSS_MODEL-STEP](#)
- [3D Models - CL501TNMHWSS_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10103051](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-CL501TNMHWSS-SPEC-EN | REV 6/2024